



## SPECIFICATION

Poles:2-24

Voltage rating:AC,DC 250V

Current rating:AC,DC,7A

Withstand voltage:1500V AC min.

Insulation resistance:1000MΩ min.

Temperature range:-25℃~+85℃

Applicable PC board thickness:0.031"~0.063"

(0.8~1.6mm)

Contact resistance:Initial value 10mΩmax.

After environmental testing 20mΩmax.

Material:Nylon66 UL94V-2

Contact:Brass

Finish:Tin-plated

Color:Nature

### TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	<b>C</b> 深圳市灿科盟实业有限公司 kmTW CHANKLEMENT INDUSTRYCO., LTD	TITLE:		5557S-2*XP 方针
CHECKED:	DATE:		CLIENT P/N	/	SCALE
DRAWN:	DATE:	UNIT	mm	REV.	A
LXF	2008-04-07	FILE NO.	Ckmtw=5557-0015	DC	HW