





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Tin Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list				
ITEM	PA	PB	PC	L
Standard	6.50	3.18	4.82	15.10
Alternate				

深圳市连盛精密连接器有限公司

REV		DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	OPERATION	SCALE	FIT	PART NO.	TITLE:
A0	2012.03.28	NEW DRAWING			Angle	±3°	APPROVE	SHEET	1/1		
					X.X	±0.30	OPERATION	UNIT	mm		
					X.XX	±0.20	CHECK	SIZE	A4		
					X.XXX	±0.10		PROJ.	☞		