






SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
 - 2、Voltage Rating: 250V AC, DC
 - 3、Temperatuer Range: -25℃~+85℃
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 1000MΩ Min
 - 6、Withstanding Voltang: 1000V AC/minute
 - 7、Material: Wafer LCP, UL94V-0
- PIN Brass Tin-plated
Solder Phosphoric bronze Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
HC-HY-2ALT	2.00	8.00
HC-HY-3ALT	4.00	10.00
HC-HY-4ALT	6.00	12.00
HC-HY-5ALT	8.00	14.00
HC-HY-6ALT	10.00	16.00
HC-HY-7ALT	12.00	18.00
HC-HY-8ALT	14.00	20.00
HC-HY-9ALT	16.00	22.00
HC-HY-10ALT	18.00	24.00
HC-HY-11ALT	20.00	26.00
HC-HY-12ALT	22.00	28.00
	38.00	44.00

制 图 DRAWN	变更内容 DESCRIPTION	日 期 DATE	GENERAL TOLERANCE		制 图 DRAWING	钱岳生 2013、07、01			料 号 PART NO.	HY-NALT		版 本 REV.	A
			X.±0.25	X.°±2°	审 核	张 名			品 名	HY立贴		页 次	1/1
					CHECK	2013、07、03			WAFER SMT TYPE	客户料号	CUTM. NO.		
						张 名							
						2013、07、05							
.X.±0.20		.X.°±1°	核 准	张 名			深圳市华灿天禄电子有限公司						
.XX.±0.15		.XX.°±0.5°	APPROVAL	2013、07、05									
.XXX.±0.10		.XXX.°±0.5°	单 位 UNITS	MM	比 例 SCALE	1:1							