


凸柄(P)



短柄(S)

- NOTE:
- 1.Rating: 24V 25mA DC
  - 2.Insulation Resistance:  $\geq 100 \text{ M}\Omega$
  - 3.Withstand voltage: AC 500V 1Minute
  - 4.Operating Force Range: 800gf Max
  - 5.Mechanical Life: 1,500 Cycles
  - 6.Operating Temperature range  $-20^{\circ}\sim+70^{\circ}\text{C}$
  - 7.Ambient Humidity used:  $\leq 85\% \text{RH}$

Position(位数)	2P	3P	4P	5P	6P	7P	8P	9P	10P	12P	
DIM.A(长度)	6.08	8.62	11.16	13.70	16.24	18.78	21.32	23.86	26.4	31.48	
DIM.B(长度)	2.54	5.08	7.62	10.16	12.70	15.24	17.78	20.32	22.86	27.94	
PART NO. 盖子/黑色(K)	凸柄(P) 短柄(S)	EM-02KP EM-02KS	EM-03KP EM-03KS	EM-04KP EM-04KS	EM-05KP EM-05KS	EM-06KP EM-06KS	EM-07KP EM-07KS	EM-08KP EM-08KS	EM-09KP EM-09KS	EM-10KP EM-10KS	EM-12KP EM-12KS

④	Terminal	—		Phosphor bronze	Au Plating	—
③	Base	—	1	PBT	Black	—
②	Cover	—	1	PBT	Black	—
①	Keystoke	—	1	PBT	White	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		HROE ELECTRONICS CO.,LTD		
DRAWN	Coco.li	2014/02/13		TITLE:	MULTIFUNCTIONAL SWITCHES	
CHECKED				PART NO.	EM-□□□□	
APPROVALS				TOLERANCES ARE	ANGLE	UNIT: mm
		30~以上	±0.30		±2'	SCALE: 1:1
		10~30	±0.20			PROJ:
		5~10	±0.15			DRAWING NO.
		~ 5	±0.10			SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			