










NOTE:
1.Rating:DC30V 0.1A
2.OP:12.8±0.8
3.Operating froce:30±15gf
4.Mechanical Life:3,000,000

⑩	Spindle	—	1	Alloy	Plating Nicke	—
⑨	Roller	—	1	POM	Black	—
⑧	Shrapnel 2	—	1	Copper Alloy	—	—
⑦	Shrapnel 1	—	1	Beryllium Copper	—	—
⑥	Contact	—	1	Copper Alloy	—	—
⑤	Lever	—	1	Stainless Steel	—	—
④	Terminal	—	3	Copper Alloy	Plating silver	—
③	Base	—	1	PBT	White	—
②	Knob	—	1	PBT	Gray	—
①	Cover	—	1	PBT	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		HRO韩荣® ELECTRONICS CO.,LTD			
DRAWN	JKUN.LU	2015.4.8					
CHECKED				TITLE:	MICRO SWITCHS		
APPROVALS				PART NO.	K9-1267P		
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
		±2°		DRAWING NO.			SHEET 1 OF 1

	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.