



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

③	Shell	—	1	STAINLESS STEEL	Ni Plated
②	Contact	—	14	COPPER ALLOY	Au Plated
①	Housing	—	1	LCP	Black
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING

APPROVALS		DATE		 ELECTRONICS CO.,LTD						
DRAWN	JIANKUN.LU	2018.08.01								
CHECKED				TITLE:	USB CONNECTOR					
APPROVALS				PART NO.	TYPE-C-31-M-19					
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm					
		10~30	±0.25							
		5~10	±0.20	±2'	SCALE: 1:1					
		~ 5	±0.15							
ECN NO.	REV.	DATE.	CHANGE.	CHECK.	APPRO.	DRAWING NO.		PROJ:		SHEET 1 OF 1

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.