


Rating: 10A 16V DC
 Contact Resistance: 30 mΩ Max.
 Operating temperature: -20℃~70℃
 Operating force: 3-15N
 Operating Life: 5,000cycles



CIRCUIT DIAGRAM

PIN	ø1.65	ø2.0	ø2.5
-----	-------	------	------

②	Terminal	—	—	Brass	Au Plating	—
②	Terminal	—	—	Iron sheet	Ni Plating	—
②	Terminal	—	—	Phosphor bronze	Sn Plating	—
①	Housing	—	1	PBT	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2013/11/11					
CHECKED			TITLE:		PHONE JACKES		
APPROVALS			PART NO.		DC-052		
TOLERANCES ARE		30~以上 ±0.30	10~30 ±0.20	ANGLE	UNIT: mm	SCALE: 1:1	
		5~10 ±0.15	~ 5 ±0.10	±2'	DRAWING NO.	PROJ:	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.