



XKB Product features

Voltage: < 12V
 Current: < 20mA
 Conduction time: 2ms
 Closed circuit resistance: < 30m ohm
 Open circuit resistance: > 10m ohm
 High temperature resistance: 240 degrees
 Terminal tension: 500gf / min
 Humidity: 95RH 40 degrees 96 hours
 Operating life: 200000 times

Product features:

- XKB 产品特性:
- SW-58010P is a sealed non-directional vibration induction starting switch, which can be triggered at any Angle.
 - SW-58010P为密封型无方向性振动感应出发开关, 任何角度均可触发
 - This series of switches in the static world is open circuit OFF state, when the external force to touch the corresponding vibration force, or moving speed to adapt to (partial) centrifugal force, conductive pin will produce instantaneous conduction and show ON state; When the external force disappears, the switch reverts to the open OFF state.
 - 本系列开关在静止世为开路OFF状态, 当受到外力碰触而达到相应振动力时, 或者移动速度达到适应(偏)离心力时, 导电接脚会产生瞬间导通而呈ON状态; 当外力消失时, 开关恢复为开路OFF状态。
 - This series switch with P model, sealed package.
 - 本系列开关带P型号, 为密封式封装。
 - This series of switch trigger sensitivity is high.
 - 本系列开关触发灵敏度高。
 - This series of switches can reach 200000 times in normal service life.
 - 本系列开关在正常使用寿命可以达到200000次。
 - This series of switches are suitable for burglar alarm, electronic scale, mobile power supply, toys and other sensor type electronic products. XKB
 - 本系列开关适用于, 防盗报警器, 电子秤, 移动电源, 玩具等系列传感类型电子产品。



⑤	Coat the brass	1	Brass	NICKE	_____
④	sealing rubber	1	Rohs epoxy resin		_____
③	Spring C	1	SUS	0.10	_____
②	Tube body B	1	Brass	silver	_____
①	Outer copper sleeve A	1	Brass	gold-plated	_____
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING	REMARK

REVISIONS					UNSPECIFIED TOLERANCES		DSND	DATE	SCALE: N/A	MODEL TYPE:		
ΔX					units: mm	DWN	DATE	VIEW:	Vibration switch			
ΔX					tolerance: X.X ±0.2mm	CHKD	DATE	UNIT: mm/in	PART NO.:			
ΔX					X.XX ±0.1mm	APPD	DATE	SIZE: A4	DWG NO.:			
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm				SW-58010PZDG-7A11S1			
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
										1.0g	1/1	A0