



STRUCTURE (构造)			
NO.	ITEM(项目)	SPECIFICATION(规格)	
1	INSULATION (胶膜)	印字:E488937 UL20624 (43μm)	
		白膜:80°C 60V(43μm)	
2	SUPPORTING TAPE (补强板)	225μm	Blue(蓝色)
3	CONDUCTOR (导体)	Thickness(厚度)	0.035 ±0.005
		Width(宽度)	0.3 ±0.03
4	CONDUCTOR (导体镀层)	PLATED(电镀)	锡Sn(1μm) MIN
		PLATED(电镀)	



DIMENSION (尺寸)			
No. of conductors (导体数目)	N	40	
Pitch(间距)	P	0.5	±0.05
Span(总间距)	SP	19.5	±0.05
Width(总宽度)	W	20.5	±0.08
Margin(边缘宽度)	M	0.5	±0.07
Total length(总长度)	TL	50	±2.0
Insert Thickness (插接端厚度)	T	0.3	±0.03
Surface Thickness (线身厚度)	ST	0.12	±0.03
Strip Length (裸铜长度)	S1	4.0	±1.0
	S2	4.0	±1.0
Supporting Tape Length(补强板长度)	B1	8.0	±2.0
	B2	8.0	±2.0



Material List(辅料清单)			
NO.	ITEM(项目)	SPEC(规格)	QTY(数量)
1			
2			
3			
4			
5			
6			

技术要求:

- 保存环境:
温度: 15~25°C 湿度: 30~50RH%
- 保质期:
镀金: 12个月 镀锡: 6个月
- 产品符合ROHS 2.0标准

Customer P/N:(客户料号):			C31030				深圳市连线电子有限公司					
NO.	DESCRIPTION(描述)	DATE	Drawing:(绘制)	Title: FPC CABLE								
01	NEW DRAWING(新作成)	2021.08.12	陈历祥	0.5*40*50*B(4/4/8/8)(0.035*0.3)			Customer(客户)		A771	Rev.(版次)	A/0	
				Dwg NO.(图纸编号)						Page(页码)	1/1	
				Unit:mm							Weight(重量)	