

PANEL CUT-OUT		
Z	Y	X
0.70~1.25	9.00~9.10	13.50~13.60
1.25~2.00	9.00~9.10	13.60~13.70

NOTES:

1. Rating:

VDE ENEC 3A 250VAC T125/55

UL cUL 6GPA 125VAC/3GPA 250VAC T105/55

CQC 3A 250VAC, 3A/40A 250VAC T105/55

2. Circuit Diagram: 2P ON-OFF

3. Terminal Strength: $\geq 40N$

4. Electrical life: ≥ 10000 cycles

5. Withstand Voltage: Withstand Voltage: 1500VAC 1min


Terminals to Button: 3000VAC 1min

Leakage Current: 1mA

6. Current resistance: $\leq 50m\Omega$ (initial)

7. Insulation resistance: $\geq 100M\Omega$

8. Body Materil: NYLON 66 94V-0~2



A4				普通公差:	深圳市华灿天禄电子有限公司								
A3				COMMON TOLERANCE :									
A2				UP TO 5	± 0.20	单位	mm	投影		品名	跷板开关	比例	Free
A1				ABOVE 5 TO 30	± 0.30	绘图	周金勇	核对	梁金勇	型号	RS601H		
				ABOVE 30	± 0.50	DRAWN BY		CHECKED BY		图号			
REV.	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	$\pm 5^\circ$	日期	2015.12.22	核准	周培雷	DWG NO.	RS601HL-1010011BB		