



P.C.B LAYOUT
BOTTOM VIEW



SCHEMATIC (NON-SHORTING)





PS-22E35XX

PUSH SWITCH

G-Switch P/N

N=NO LOCK
L=LOCK

- A=黑色
- B=红色
- C=蓝色
- D=其它



注：“*”表示关键尺寸(7个).

G-Switch Specification:
 Electrical Specifications: 0.5A 30VDC
 Contact Resistance: ≤100mΩ
 Insulation Resistance: ≥100MΩ DC125V
 Withstand Voltage: AC125V 1 minute
 Operating Temperature: -25°C~+65°C
 Storage Humidity: ≤85%RH
 Electrical Life: 10,000
 Mechanical Life: 100,000



G-Switch Electronic (HongKong) CO.,Ltd.

Unless otherwise specified, Tolerance:	±0.30	DESIGN	Bright Lee	DATE	2016.05.29	Mold code:	
X	±0.20	CHECKED		DATE		PS-22E35	
X.XX	±0.15	APPROVED		DATE			
X.XXX	±0.10						
Angles	±3						
		http://www.dg-switch.com		REV.:	X1	SCALE:	4:1
		TEL:0769-82388879		SIZE:	A4	SHEET:	1/1

A B C D E

5 4 3 2 1