



**Technology Request:**

1. Outlook: No burr, no hurt.
2. Electronic performance:
  - a: Insulation resistance: Above DC500V/100M Ω;
  - b: Endure voltage: AC500V at 1 minute;
  - c: Contact resistance: Under 30m Ω;
3. Insertion force & withdrawal force: 0.3-3kgf.
4. Salt spray test: 48H.
5. Meet RoHS.
6. Remark \* is important specification.

	MATERIAL	PLATING
Terminal	phosphor bronze	NI
Fork hook tube	H65	NI
Plastic	Pbt	Black

					DSND	DATE	SCALE: N/A	MODEL TYPE:		
ΔX					ANGLAR		VIEW:	DC PIUG		
ΔX					X.X		UNIT: mm	PART NO.: DT-2306530		
ΔX					X.XX		SIZE: A4	DWG NO.:		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX					
REVISIONS					UNSPECIFIED TOLERANCES					
www.xk-dg.cn www.helloddb.com www.helloddb.cn					XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
								1.0g	1/1	A0