


P.C.B LAYOUT



MODEL CODE

SS22F07 - X

L (mm)
2 ~ 10

RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100mΩ MAX.
TRAVEL	2mm
OPERATING FORCE	250±100gf
OPERATING LIFE(cycles)	10,000

					DSND		DATE		SCALE: N/A	MODEL TYPE: SLIDE SWITCH		
					DWN		DATE		VIEW:	PART NO.: SS22F07		
					CHKD		DATE		UNIT: mm	DWG NO.: SS22F07X		
					APPD		DATE		SIZE: A4			
Δx					ANGLAR	±5°						
Δx					L ≤ 4	±0.2						
Δx					4 < L ≤ 16	±0.3						
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4						
					L > 63	±0.5						
REVISIONS					UNSPECIFIED TOLERANCES							
www.xk-dg.cn www.1k0k.com www.1k0k.cn					XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT	SHEET	REVISION
										1.0g	1/1	A0