



■ Specifications :

- Voltage rating: 350V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -55°C~+105°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤20mΩ
- After environmental testing:≤40mΩ

X1515 H- XX-N0  
① ② ③ ④

- ① SeriesNumber
- ② Category : H-HSG
- ③ Row No.Pin No:02-15P
- ④ Material:N0-PA66 94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.50	4.10	3.70	09	12.00	14.60	14.20
03	3.00	5.60	5.20	10	14.0	16.10	15.70
04	4.50	7.10	6.70	11	15.0	17.60	17.20
05	6.00	8.60	8.20	12	17.0	19.10	18.70
06	7.50	10.10	9.70	13	19.0	20.60	20.20
07	9.00	11.60	11.20	14	24.0	22.10	21.70
08	10.50	13.10	12.70	15	24.0	23.60	23.20

X1511H-XX-N0	PA66 UL 94V-0	X1511T	X1511W
PARTY NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

DSND		DATE		SCALE: N/A	MODEL TYPE: X1511H-XX-N0
DWN		DATE		VIEW:	PART NO.: 1.5mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	DWG NO.:
APPD		DATE		SIZE: A4	
UNSPECIFIED TOLERANCES					WEIGHT
XKB INDUSTRIAL PRECISION CO.,LIMITED					SHEET
					REVISION
					1.0g
					1/1
					A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5