

()	
_	_	ì	
	_	7	
i	ı	ı	
٠	٠		

REV.

MATTER


APP.

DATE

1.MATERIAL:
a.HOUSING:THERMOPLASTIC GLASS FIBRE UL94V-0
b.CONTACT:Phosphor bronze c.Plating:SN100~120U",

2.ELECTRIC:

d.CONTACT RESISTANCE: 30 MILLIOHMS MAX
 b.INSULATION RESISTANCE: 1000 MEGA OHMS MIN
 c.DIELECTNIC VOLTAGE: 750V AC ONE SEC LEVEL
 d.OPERATING TEMPERATURE: -30~C~ +80~C




3.6±0.1⊐

3,6±0,1 ┙

 7.5 ± 0.1

8,6,±0,1





SECTION A-A

深圳市琦捷电子有限公司

.xxx ±0.10	.x ±0.38 .xx ±0.25	×. ±1	LINCAN		TOLERANCE	
Ė	.×. ±2.		ANGLE		NCE	
DATE 2021.06.06		ATTROVED		\	DRAWN	
SIZE: A4	SCALE:	MM	UNIT:	+	ф Д	
DWG. NO. QJ-BS-2-1	a	PART NO. QJCR2032-2-1(3.6)		TITLE: 阻燃电池座QJ (BS-2-1)		
SHEET. 1 OF 1	Α	REV.				