



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2001-02AW	2.00	6.00
A2001-03AW	4.00	8.00
A2001-04AW	6.00	10.00
A2001-05AW	8.00	12.00
A2001-06AW	10.00	14.00
A2001-07AW	12.00	16.00
A2001-08AW	14.00	18.00
A2001-09AW	16.00	20.00
A2001-10AW	18.00	22.00
A2001-11AW	20.00	24.00
A2001-12AW	22.00	26.00
A2001-16AW	30.00	34.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENEAL TOLERANCE		制图 DRAWING	贺骏驹 2013、07、01	料号 PART NO.	A2001-NAW	版本 REV.	A
			X.±0.25	X.'±2'	审核 CHECK	赖积任 2013、07、03	品名 TITLE	PH弯针 WAFER DIP TYPE	页次 SHEET	1/1
			.X±0.20	.X'±1'	核准 APPROVAL	张松强 2013、07、05	客户料号 CUTM. NO.			
			.XX±0.15	.XX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1		
			.XXX±0.10	.XXX'±0.5'					KH-PH-4P-W	0755-83044319