










REV.	ECN NO.	REVISED	DATE



工程部
2020-11-03
LQ. HUANG

技术要求:

- 1、截断面毛刺高度 $\leq 0.03\text{mm}$;
- 2、部件要求平整,无变形、裂纹、损伤等外观缺陷;

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	YangFeng	DATE	2020-11-03
		CHKD	ZhouRuicai	DATE	2020-11-03
		APVD	XueShunyong	DATE	2020-11-03
		WEIGHT:	g	SCALE:	SIZE: A4
		SHEET 1 OF 1		VIEW:	
				REV.:	A/0
				OBJECT:	MY
				TITLE: 电池扣CR2032-D01 DIP	
				PART NO.: MY-2032-22	
				DRAW NO.:MY-CP-0251	

1	TERMINAL+	1	SPCC T=0.3mm	Ni-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR