


Temperature -20~70 C
 Rated Load DC 30V 0.3A
 Contact Resistance <0.03Ω
 Insulation Resistance >100MΩ
 Withstand Voltage AC500V(50Hz)/min
 Actuating Force 2.2~30N
 Life 3000次

color B:Black W:White

	MATERIAL	PLATING
terminal 1	Phosphor Bronze	silver
terminal 2	Phosphor Bronze	silver
terminal 3	Phosphor Bronze	silver
terminal 4	Phosphor Bronze	silver
terminal 5	Phosphor Bronze	silver
plastic	Pbt	



广东星坤科技股份有限公司

生效日期

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

文件工程章

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.: PJ-358H-X
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0

www.helloxkb.cn www.helloxkb.com www.helloxkb.cn