


CIRCUIT DIAGRAM

NOTE:



Rating: DC 12V 50mA

Operating Force: 200±100gf

Lifetime: 10,000 Cycles



PCB LAND PATTERN



PAPT NO	L	Color
SS-3292S-L1	1.5	B:black
SS-3292S-L2	2.0	W:white
SS-3292S-L3	3.0	

ITEM	PAPT NAME	TER,NO	QTY	MATERIAL	FINISHING	REMARK
5	Terminal	7		Brass (0.30t)	ag Plated	
4	Contact spring	1		Phosphor branze	ag Plated	
3	Base	1		Lcp	Black	
2	Cover	1		Sus	Natural	
1	Keystake	1		Pa46	Black	

广东星坤科技股份有限公司

生	日期
效	
效	
效	
MARK	文件工程章

DESCRIPTION	DATE	REVISED	APPROVED	units: mm
				tolerance:
				X.X ±0.2mm
				X.XX ±0.1mm
				X.XXX ±0.05mm
UNSPECIFIED TOLERANCES				

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	SLIDE SWITCH
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.: SS-3292S-X-X
KKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT SHEET REVISION
			1.0g 1/1 A0