






NOTES:

1.0 RATING

1.1 TEMPERATURE:-25°C TO +75°C;

2.1 INSULATION RESISTANCE:100M AT 500V DC

2.2 DIELECTRIC STRENGTH:AC 500V,60Hz FOR 1MINUTE;

3.0 MATERIALS


3.1 HOUSING:THERMOPLASTIC;

3.2 CONTACT:COPPER ALLOY

4.0 INSERTION &EXTRACTION FORCE

4.1 INSERTION &EXTRACTION:1.0 TO 2.5kgf;

AFTER LIFE TEST:0.3 TO 2.5 kgf;



	MATERIAL	PLATING
terminal 1	Phosphor Bronze	tin
terminal 2	Phosphor Bronze	tin
terminal 3	Phosphor Bronze	tin
terminal 4	Phosphor Bronze	tin
terminal 5	Phosphor Bronze	tin
terminal 6	Phosphor Bronze	tin
plastic	Pbt	

广东星坤科技股份有限公司

生效日期

MARK DESCRIPTION

文件工程章

REVISIONS

www.helloxkb.cn www.helloxkb.com www.helloxkb.cn

DATE REVISED APPROVED

ANGLAR ±5°
L ≤ 4 ±0.2
4 < L ≤ 16 ±0.3
16 < L ≤ 63 ±0.4
L > 63 ±0.5

UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.: PJ-378B
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0