








- Specification:
1. Rating : DC 30V 0.5A;
 2. Contact resistance: $\leq 30m\Omega$;
After life test: $\leq 50m\Omega$
 3. Insulation resistance: $\geq 100M\Omega$ (500VDC);
After life test: $\geq 50M\Omega$
 4. Withstand voltage: 500VAC ;
 5. Insertion and extraction force: 3N~25N;
 6. life test: 5000cycles min;
 7. Operation temperature range: $-20^{\circ}C \sim 70^{\circ}C$
 8. Preservative temperature range: $-40^{\circ}C \sim 85^{\circ}C$
 9. Sign"▲" is importance dimension



	MATERIAL	PLATING
terminal 1	copper alloy	silver
terminal 2	copper alloy	silver
terminal 3	copper alloy	silver
terminal 4	copper alloy	silver
plastic	PA9T	

广东星坤科技股份有限公司

生效日期

MARK DESCRIPTION

REVISIONS

www.hellokx.com www.hellokx.com www.hellokx.com

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.: PJ-315X
APPD		DATE		SIZE: A4	WEIGHT SHEET REVISION 1.0g 1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED

文件工程章