



### FEATURES

- Light operating force.
- Long term low contact resistance.
- Momentary or latching operation.
- Short stroke 3.0mm to latch.

### SPECIFICATIONS

#### 1.ELECTRICAL

● Contact rating	0.3A, 50VDC
● Contact resistance	50mWMax
● Insulation resistance	100MWMin. at 250VDC
● Dielectric strength	250VAC Min. for 60 sec.

#### 2.MECHANICAL AND ENVIRONMENTAL

● Temperature rating	Operating: -15°C to +55°C Storage: -25°C to +65°C
● Operation force	250±80gf
● Stroke	Lock Stroke: 3.0±0.3mm Full Stroke: 3.5±0.3mm
● Operating life	full load: 1x10 <sup>4</sup> cycles no load: 1x10 <sup>5</sup> cycles

PAPT NO	XKBS22E05-X
OPERATION	W:NO LOCK Z:LOCK

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑦	Bottom plate	—	1	Phenolic Resin	Natural	—
⑥	Contact	—	2	Phosphor bronze	ag Plated	—
⑤	Terminal	—	6	Brass	Plating silvering	—
④	Spring	—	1	Sus	Natural	—
③	Base	—	1	Spcc	Plating Nickel	—
②	Crochet Needle	—	1	Sus	Natural	—
①	Keystake	—	1	Pa66		—

广东星坤科技股份有限公司

常态: 1-2导通 4-5导通  
按下: 2-3导通 5-6导通

生效	日期
ΔX	
ΔX	
ΔX	

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	KEY SWITCH
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT
			1.0g
			SHEET
			1/1
			REVISION
			A0

文件工程章

REVISIONS  
UNSPECIFIED TOLERANCES  
www.helloxkb.com www.helloxkb.cn