

XXB Connectivity

■ 规格 Specifications:

- 额定电压 Voltage rating: 250VAC/DC.
- 额定电流 Current rating: 3A AC/DC
- 耐电压 Withstanding voltage: 1000V AC/minute
- 温度区间 Temperature range: -40°C to +105°C
- 绝缘电阻 Insulation resistance: ≥1000MΩ Min
- 接触电阻 Contact resistance: ≤20MΩ Max
- 材料 Material: PA6T 94V-0
- 镀层 Plating Category: 1U" Gold
- 波峰焊温度 Wave soldering temperature: 255±5°C, 10s

XXB Connectivity


X6521 F V- 2*XX - C85 D32

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: F-Female
- ③ Welding Board Angle: V-Stright 180°
- ④ Row No -Pin No: 2*XX-2*01P-40P
- ⑤ Plastic height: C=8.5mm
- ⑥ Plastic length: D=3.2mm

XXB Connectivity

X6521FV-2*XX-C85D32	PA6T 94V-0	Brass	1U"Gold	X6521W
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XXB Terminal



PCB LAYOUT

XXB Connectivity

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

www.xkb.cn www.helloxkb.com www.helloxkb.cn

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: X6521FV-2*XX-C85D32
DWNN	DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connector
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0