



Specifications:  
 规格:  
 Voltage rating:250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating:3A AC/DC  
 额定电流: 3A AC/DC  
 Withstanding voltage:1000V AC/minute  
 耐受电压: 1000V AC/分钟  
 Temperature range:-25°C~+85°C  
 温度范围: -25°C~+85°C  
 Insulation resistance:≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
 Contact resistance:≤30mΩ  
 接触电阻: ≤30mΩ  
 After environmental testing:≤50mΩ  
 环境测试后: ≤50兆欧

X2026 T X - P SN X - D  
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series Number
- 2.Category:T-terminal
- 3.Appearance type:Blank-Ordinary
- 4.Material:P-Phosphor bronze
- 5.Plating style:
- 6.SN-Bright tin plating;G03-Contact Gold Plating 3u"
- 7.Plating method:Blank-Stamping before plating  
 Mold No/Mark/Special No:  
 D-Mating 2026H-2x08D Series Following Housing

poles	Dimensions(mm)			poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	4.60	6.76	2x10	18.00	20.60	22.76	2x18	34.00	36.60	38.76
2x03	4.00	6.60	8.76	2x11	20.00	22.60	24.76	2x19	36.00	38.60	40.76
2x04	6.00	8.60	10.76	2x12	22.00	24.60	26.76	2x20	38.00	40.60	42.76
2x05	8.00	10.60	12.76	2x13	24.00	26.60	28.76				
2x06	10.00	12.60	14.76	2x14	26.00	28.60	30.76				
2x07	12.00	14.60	16.76	2x15	28.00	30.60	32.76				
2x08	14.00	16.60	18.76	2x16	30.00	32.60	34.76				
2x09	16.00	18.60	20.76	2x17	32.00	34.60	36.76				

X2026T-PG03-D	Phosphor Bronze	AWG#22-28	1.60mm(Max)	Stamping Before plating;30u"MIN.Ni ;Contact3U"Au	X2026H-D
X2026T-PSN-D	Phosphor Bronze	AWG#22-28	1.60mm(Max)	Stamping Before plating;30u"MIN.Ni ;70u"Sn	X2026H-D
PART NO	Material	Wire Range	Insulation OD	Finish	Suitable XKB

广东星坤科技股份有限公司

生	日期
ΔX	ΔX
ΔX	ΔX
MARK	文件工程章
DESCRIPTION	REVISIONS
DATE	REVISED
APPROVED	UNSPECIFIED TOLERANCES
www.xk-dg.cn	www.helloxkb.com
www.helloxkb.com	

DSND	DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	2.00mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.: X2026T-PXXX-D
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
			SHEET
			REVISION
			1.0g
			1/1
			A0