



Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -40°C~+105°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10m Ω
- After environmental testing : ≤20mΩ

X3025 W R X - XX C - XX SN XX
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : W-wafer
- ③ Welding Board Angle: R-90°
- ④ Welding Way: Blank-DIP
- ⑤ Row No.-Pin No.: XX-01P-12P
- ⑥ Plug the Pin & Special No.: C-The harpoon
- ⑦ Material : LP-LCP 94V-0 ; 66-PA66 94V-0
- ⑧ Planting Category: SN-Bright tin plating
- ⑨ Color : Blank-Natural Color Black

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
01	---	6.65	07	18.00	24.65
02	3.00	9.65	08	21.00	27.65
03	6.00	12.65	09	24.00	30.65
04	9.00	15.65	10	27.00	33.65
05	12.00	18.65	11	30.00	36.65
06	15.00	21.65	12	33.00	39.65

X3025WR-XXC-66SN	PA66 UL 94V-0	Brass	Tin-Plated	X3025H
X3025WR-XXC-LPSN	LCP UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With(XKB Housing)

Recommended P.C.B Layout

Sheet Title traces:05

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

www.helkxb.com

XKB	ANGLAR	±5°
L ≤ 4		±0.2
4 < L ≤ 16		±0.3
16 < L ≤ 63		±0.4
L > 63		±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWVN	DATE	VIEW:	X3025WR-XXC-XXSN
CHKD	DATE	UNIT: mm/in	PART NO.: 3.00mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0