

Specifications:

规格:
Voltage rating: 50V AC/DC
额定电压: 50V AC/DC
Current rating: 1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage: 250V AC/minute
耐压电压: 250V AC/minute
Temperature range: -25°C ~ +85°C
温度范围: -25°C ~ +85°C
Insulation resistance: ≥100MΩ
绝缘电阻: ≥100MΩ
Contact resistance: ≤20mΩ
接触电阻: ≤20mΩ
After environmental testing: ≤20mΩ
环境测试后: ≤20mΩ

X1259 T X- P SN X-X

① ② ③ ④ ⑤ ⑥ ⑦

① Series Number

② Category:

③ Shape:

④ Material:

⑤ Planting style

⑥ Planting method:

⑦ Mold No./Mark/Special No.


T-terminal

Blank-ordinary

P-Phosphor bronze

SN-Bright tin plating

Blank-Stamping before plating



X1259T-PSN	Phosphor Bronze	AWG#28-32	1.00MM(MAX)	Stamping Before Plating: 30u"MIN.Ni;70u"Sn	1259H
PART NO	Material	Material(Pin)	Finish(Pin)	Finish	Used In XKB Housing

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

www.xkb.com.cn www.hellixkb.com www.hellixkb.com

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWNN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	1.25 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			X1259T-PSN
WEIGHT		SHEET	REVISION
1.0g		1/1	A0