





XXB



SECTION A-A  
SCALE 1:1



SECTION B-B  
SCALE 1:1



Specifications:

规格: XKB  
 Voltage rating: 600V AC/DC  
 额定电压: 600V AC/DC  
 Current rating: 9A AC/DC  
 额定电流: 9A AC/DC  
 Withstanding voltage: 1500V AC/minute  
 耐受电压: 1500V AC/分钟  
 Temperature range: -25°C +85°C  
 温度范围: -25°C +85°C  
 Insulation resistance: ≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
 Contact resistance: ≤10mΩ  
 接触电阻: ≤10mΩ  
 After environmental testing: ≤20兆欧  
 环境测试后: ≤20兆欧

X9357 WR X-2 XX X-XX XX XX  
 ① ② ③ ④ ⑤ ⑥ ⑦

X9357TM-X SNX-X

① ② ③ ④ ⑤ ⑥ ⑦

- 1 Series No.
- 2 Category: T-Terminal
- 3 Appearance type: M-Male Terminal
- 4 Material: B-Brass; P-Phosphor Bronze
- 5 Plating Style: SN-Bright Tin Plating
- 6 Plating Method:  
Blank-Stamping before Plating
- 7 Mold NO/MARK&Special NO

X9357TM-PSN	Phosphor Bronze	AWG#18-22	3.00mm(Max)	Stamping Before Plating 30u" Ni/0u" Sn	X9357HF
X9357TM-BSN	Brass				
PART NO	Material	Wire Range	Insulation O D	Finish	Suitable XKB

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

www.helxkb.com

DSND	DATE	SCALE: N/A	MOLD TYPE: X9357TM-XSN
DWNN	DATE	VIEW: ①	PART NO.: 2.40mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0