



■ Specifications :

- Voltage rating: 100V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -40°C~+85°C
- Insulation resistance: ≥500MΩ
- Contact resistance: ≤20mΩ
- After environmental testing : ≤40mΩ

X1515 W R S-XX-LP SW

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : R-Straight 90°
- ④ Welding Way:S-SMT
- ⑤ Row No.-Pin No.: XX-02P~15P
- ⑥ Material : LP-LCP 94V-0
- ⑦ Plating Category: SW-Matte Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	7.30	1.50	4.45	09	17.80	12.00	14.95
03	8.80	3.00	5.95	10	19.30	13.50	16.45
04	10.30	4.50	7.45	11	20.80	15.00	17.95
05	11.80	6.00	8.95	12	22.30	16.50	19.45
06	13.30	7.50	10.45	13	23.80	18.00	20.95
07	14.80	9.00	11.95	14	25.30	19.50	22.45
08	16.30	10.50	13.45	15	26.80	21.00	23.95

X1515WRS-XX-LPSW	LCP UL 94V-0	Phosphor Bronze	Brass	Matte Tin-Plated	X1515H
PART NO	Material	Material(pin)	Material	Finish(pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效  

ΔX		日期
ΔX		
ΔX		
MARK	DESCRIPTION	

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X1515WRS-XX-LPSW
CHKD	DATE	UNIT: mm/in	PART NO.: 1.5mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn