




(LOCATION OF CARD PUSHED)0.20 [0.008]
 (LOCATION OF CARD EJECTED)4.45 [0.175]
 (LOCATION OF CARD LOCKED)1.00 [0.039]




- NOTES:
 1.SPECIALITY:
 1.1 Rated current: 1.0A
 1.2 Rated voltage: 30V
 1.3 Contact Resistance: 50mΩ MAX
 1.4 Insulation Resistance: 1000MΩ MIN 500V DC
 1.5 Dielectric withstanding voltage: 500V AC.
 1.6 Solder ability: 250±5℃ 15±0.0s.
 1.7 Durability: 1000 Cycles Min.
 1.8 Operating condition: Temperature: 40℃ ~ +65℃ ; Humidity: 80% R.H MAX

ELECTRIC FUNCTION	DETECT SWITCH
WITHOUT CARD	CLOSED
CARD INSERTED	OPEN



3FF SIM CARD	
Pin NO.	NAME
C1	VCC
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	VPP
C7	I/O
C8	Reserved



RECOMMENDED P.C.B LAYOUT
 COMPONENT SIDE(TOLERANCE ±0.05)
 PAD AREA
 KEEP OUT AREA

ITEM	PART NAME	Q'TY	MATERIAL	FINISHING
1	HOUSING	1	HI-TEMP.PLASIC	Black UL94V-0
2	TERMINAL	7	COPPER ALLOY	Contact area: Gold plated
3	CD SWITCH	1	COPPER ALLOY	Contact area: Gold plated
4	SHELL	1	SUS	SMT area: Gold plated
5	SPRING	1	SWP	
6	HEART CAM	1	HI-TEMP.PLASIC	Black UL94V-0
7	CAM PIN	1	SUS	

广东星坤科技股份有限公司

生 效 日期

文件 工程 章

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	SIM CARD CONN
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT SHEET REVISION
			1.0g 1/1 A0