





Notes:

- 1.Dimension shall be interpreted per ASME Y14.5 M1994.
- 2.Dimension marked ▽ & ▼ should be checked by Q.C.and process, engineers and ▽ should also check the CPK data.

Specification:

1. Current Rating: 1.5 A Max
2. Voltage Rating: 30V AC,DC
3. Dielectric Strength: 100V AC RMS for 1 minute.
- 4.Contact Resistance: 50 mΩ Max.
5. Insulator Resistance: 100M Ω Min.
6. Mating/Unmating cycles: 6000cycles
- 7.Temperature: -30°Cto+80°C



ITEM	PAPT NAME	QTY	MATERIAL	FINISHING
③	Shell	1	SUS	T=0.25mm
②	Contact	5	Copper alloy	T=0.2mm
①	Housing	1	HI-TEMP.PLASIC UL 94V-0	BLACK

广东星坤科技股份有限公司

生效日期

MARK DESCRIPTION

文件工程章

REVISIONS
www.helloxkb.com www.helloxkb.cn

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: MICRO USB
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	U-E-M5SS-W-6
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0