



Specifications

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M \Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing : $\leq 20m\Omega$

X3025W V X-XXC-XXSNXX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
 ② Category :
 W-wafer
 Welding Board Angle:
 V-180°
 Welding Way:
 Blank-DIP
 ③ Row No.-Pin No.
 XX-Single row
 ④ Special NO.
 C-With a harpoon
 ⑤ Material :
 LP-LCP 94V-0 66-PA66 94V-0
 ⑥ Planting Category:
 V** : All Gold-Plated
 G** : Gold-Plated Contact
 *01-Gold Flash ; *02-2u" ; *03-3u" ; *05-5u"
 *10-10u" ; *15-15u" ; *30-30u" ; *50-50u"
 SN-Bright tin plating 70u"
 SN1-Bright tin plating 120u" Min. ;
 SW-Fog Tin plating
 ⑦ Color :
 Blank-natural color

Poles	Dimensions (mm)	
	A	B
2	3.00	9.65
3	6.00	12.65
4	9.00	15.65
5	12.00	18.65
6	15.00	21.65
7	18.00	24.65
8	21.00	27.65
9	24.00	30.65
10	27.00	33.65
11	30.00	36.65
12	33.00	39.65

X3025WV-XXC-66SN	PA66 UL 94V-0	Brass	Tin-Plated	X3025H
X3025WV-XXC-LPSN	LCP UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

广东星坤科技股份有限公司
 2-10085
 PCB LAYOUT
 日期
 文件工程章
 REVISIONS
 www.heloxkb.com

DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE:
DWN	DATE	VIEW:	X3025WV-XXC-XXSN
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	3.00 mm Crimp Style Connectors
			DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT
			1.0g
			SHEET
			1/1
			REVISION
			A0