



Specifications:

规格:
Voltage rating: 50V AC/DC
额定电压: 50V AC/DC
Current rating: 1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage: 250V AC/minute
耐压电压: 250V AC/分钟
Temperature range: -25°C ~ +85°C
温度范围: -25°C ~ +85°C
Insulation resistance: ≥100MΩ
绝缘电阻: ≥100MΩ
Contact resistance: ≤10mΩ
接触电阻: ≤10mΩ
After environment testing: ≤20mΩ
环境试验后: ≤20mΩ

X1259 H V -XX X-N0 XX

- ① ②③ ④ ⑤ ⑥ ⑦
- ① Series No.
- ② Category: H-HSG
- ③ Welding Board Angle: V-Straight 180°
- ④ Row No.-Pin No.: XX-02P-15P
- ⑤ Plug the Pin & Special No.
- ⑥ Material: NO-PA66 94V-0
- ⑦ Color: Blank-Natural Color

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	1.25	3.05	9	10.00	11.80
3	2.50	4.30	10	11.50	13.05
4	3.75	5.55	11	12.50	14.30
5	5.00	6.80	12	13.75	15.55
6	6.25	8.05	13	15.00	16.80
7	7.50	9.30	14	16.25	18.05
8	8.75	10.55	15	17.50	19.30

X1259HV-XX-N0	Nylon 66 UL 94V-0	1259BT
PART NO	Material	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

www.xkb.cc www.hellixkb.com www.hellixkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWNN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	1.25mm Board in Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			X1259HV-XX-N0
		WEIGHT	SHEET
		1.0g	1/1
		REVISION	A0