

Housing Material: PBT UL94V-0, black/White
 Contact Terminal: C2680
 Metallic Shell: Spcc430

CONTACT: UNDER PLATED 50u" MIN. NICKEL ALL
 OVER 100u" MIN. TIN IN SOLDERING
 AREA GOLD PLATED IN CONTACT AREA.

Salt Spray Test Requirements: Test 12H
 High temperature resistance of gelatinous heart: 200°~220°

Contact Resistance:
 30 milliohms MAX
 Dielectric Withstanding Voitage:
 500 V AC AT Sea Level

Insulation Resistance:
 1000MEGA ohms MIN

U221-04XN-1BU07-X1

- 1:Au 1U"
- 5:Au 15U"
- 6:Au 30U"
- 1:SPCC
- S:Scrolls F:Flat
- W:WHITE B:BLACK
- 1:PBT
- 2:PA6T
- 3:PA9T
- 4:LCP

广东星坤科技股份有限公司

生 日期



MADE IN CHINA
 文件工程章

REVISIONS
 DATE REVISED APPROVED
 www.xkb.cn www.hellixkb.com www.hellixkb.cn

ANGLR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: USB 2.0
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: U221-04XN-1BU07-S1
APPD	DATE	SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED			1.0g 1/1 A0



Housing Material: PBT UL94V-0, black/White
 Contact Terminal: C2680
 Metallic Shell: Spcc430

CONTACT: UNDER PLATED 50u" MIN. NICKEL ALL
 OVER 100u" MIN. TIN IN SOLDERING

AREA GOLD PLATED IN CONTACT AREA.

Salt Spray Test Requirements: Test 12H

High temperature resistance of gelatinous heart: 200°~220°

Contact Resistance.



30 milliohms MAX

Dielectric Withstanding Voltage:

500 V AC AT Sea Level

Insulation Resistance:

1000MEGA ohms MIN



U221-04XN-1BU07-X1

- 1:SPCC
- S:Scrolls F:Flat
- W:WHITE B:BLACK
- 1:PBT
- 2:PA6T
- 3:PA9T
- 4:LCP
- 1:Au 1U"
- 5:Au 15U"
- 6:Au 30U"

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

DATE REVISED APPROVED UNSPECIFIED TOLERANCES

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

DSND	DATE	SCALE: NA	MODEL TYPE: USB 2.0
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: U221-04XN-1BU07-F-1
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT SHEET REVISION 1.0g 1/1 A0