


规格 Specifications:

- 额定电压 Voltage rating: 250VAC/DC.
- 额定电流 Current rating: 2A AC/DC
- 耐电压 Withstanding voltage: 1000V AC/minute
- 温度区间 Temperature range: -40°C to +105°C
- 绝缘电阻 Insulation resistance: ≥ 1000MΩ Min
- 接触电阻 Contact resistance: ≤ 20MΩ Max
- 材料 Material: PA6T 94V-0
- 镀层 Plating Category: 1U"Gold
- 波峰焊温度 Wave soldering temperature: 255 ± 5°C 10s

X4611 F V- XX - C43 D28

① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category: F-Female
- ③ Welding Board Angle: V-Stright 180°
- ④ Row No -Pin No: XX-01P-40P
- ⑤ Plastic height: C=4.3mm
- ⑥ Pin length: D=2.8mm



X4611FV-XX-C43D28	PA6T 94V-0	Brass	1U"Gold	X4611W
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司 P.C.B LAYOUT XKB Connectivity

生	日期
發	
Δ	
文件工程章	

REVISIONS

DATE	REVISED	APPROVED

UNSPECIFIED TOLERANCES

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

www.xkb.cn www.hellixkb.com www.hellixkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE: X4611FV-XX-C43D28
DWNN	DATE	VIEW:	PART NO.: 2.00mm Crimp Style Connector
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0