



SPECIFICATION

Contact Rating: 50mA, 12V DC
 Contact Resistance: 100mΩ max
 Insulation Resistance: 100mΩ min. 500V DC
 Dielectric Strength: 250V AC/1minute
 Travel: 0.25mm
 Operating Temp: -40°C ~ +90°C
 Storage Temp: -30°C ~ +80°C

PAPT NO	TC-111A-X
Operating Force	A:130gf B:200gf C:300gf D:500gf
Height	H:6.65



P.C.B Mounting hole dimensionis



It is suggested to use P.C.B Board of 1.6mm thick

ITEM	PAPT NAME	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	2	Brass (0.30t)	Plating silvering	
④	Contact	1	F.ag/SUS	Natural	
③	Base	1	Pa46		
②	Cover	1	Brass	Plating Nickel	
①	Keystake	1	Steel ball		

广东星坤科技股份有限公司

生效日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	DESCRIPTION

UNSPECIFIED TOLERANCES: www.helloxb.com www.helloxb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE: TACT SWITCH
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: TC-111A-X
APPD	DATE	SIZE: A4	WEIGHT: 1.0g
XKB INDUSTRIAL PRECISION CO., LIMITED			SHEET: 1/1
			REVISION: A0