


Pin	A	B	C	D
2	1.00	3.15	7.2	9.1
3	2.00	4.15	8.2	10.1
4	3.00	5.15	9.2	11.1
5	4.00	6.15	10.2	12.1
6	5.00	7.15	11.2	13.1
7	6.00	8.15	12.2	14.1
8	7.00	9.15	13.2	15.1
9	8.00	10.15	14.2	16.1
10	9.00	11.15	15.2	17.1
11	10.00	12.15	16.2	18.1
12	11.00	13.15	17.2	19.1
13	12.00	14.15	18.2	20.1
14	13.00	15.15	19.2	21.1
15	14.00	16.15	20.2	22.1
16	15.00	17.15	21.2	23.1
17	16.00	18.15	22.2	24.1
18	17.00	19.15	23.2	25.1
19	18.00	20.15	24.2	26.1

Pin	A	B	C	D
20	19.00	21.15	25.2	27.1
21	20.00	22.15	26.2	28.1
22	21.00	23.15	27.2	29.1
23	22.00	24.15	28.2	30.1
24	23.00	25.15	29.2	31.1
25	24.00	26.15	30.2	32.1
26	25.00	27.15	31.2	33.1
27	26.00	28.15	32.2	34.1
28	27.00	29.15	33.2	35.1
29	28.00	30.15	34.2	36.1
30	29.00	31.15	35.2	37.1
31	30.00	32.15	36.2	38.1
32	31.00	33.15	37.2	39.1
33	32.00	34.15	38.2	40.1
34	33.00	35.15	39.2	41.1
35	34.00	36.15	40.2	42.1



1.FPC NOT MATING CONDITION BANNED CLOSURE  
2.PART NO. LEGEND.

X10C25 XX X P  
① ② ③

- ① Series Name : X10C25=1.0 mm Pitch(H=2.5mm)
- ② Number of terminals : XX=02-35PIN
- ③ Plating : G:Gold Flash Over Nickel T:Tin Over Nickel

3.PERFORMANCE:

- 3.1: CURRENT RATING:0.5A/PIN
- 3.2: VOLTAGE RATING:50V(AC/DC)
- 3.3: CONTACT RESISTANCE: INITIAL VALUE 30mOHM Max.
- 3.4:INSULATION RESISTANCE:500MOHM Min.
- 3.5:DIELERIC WITHSTANDING VOLTAGE:250V AC FOR 1MINUTE
- 3.6:DURABILT: 20 TIMES Min
- 3.7:OPERATING TEMPERATURE:-40~+85℃  
OPERATING HUMIDITY RANGE:20% TO 85%

广东星坤科技股份有限公司

生效日期

MARK	DESCRIPTION	DATE	REVISED	APPROVED	REVISIONS

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: FPC CONNECTOR
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	X10C25XXXP
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT SHEET REVISION 1.0g 1/1 A0