




(Ø3.5mm DC PLUG DETAIL DRAWING)



SCHEMATIC








3D VIEW

NOTES:

注释:

- 1.CONTACT CURRENT RATING: 1.5A.
触点额定电流: 1.5A.
- 2.CONTACT RESISTANCE:60 mΩ MAX.
接触电阻: 最大60 mΩ.
- 3.INSULATION RESISTANCE:100MΩ MIN.
绝缘电阻: 最小100MΩ.
- 4.DIELECTRIC WITHSTANDING:500V AC MIN.
耐介质: 最小500V AC.
- 5.DURABILITY:5.000 CYCLES MIN.
耐久性: 至少5,000次循环.

- 6.CONNECTOR MATING FORCES:2.94~29.4N(0.30~3.00Kgf);
连接器配合力: 2.94~29.4N (0.30~3.00Kgf) ;
- 7.CONNECTOR UNMATING FORCES:2.94~29.4N(0.30~3.00Kgf)
连接器脱离力: 2.94~29.4N (0.30~3.00Kgf)
- 8.WATERPROOF STRENGTH:IP-X7
防水强度: IP-X7



	MATERIAL	PLATING
plastic	Pa66	
bond		
center pin	Brass	tin
terminal 2	Brass	tin
terminal 3	Phosphor Bronze	tin

广东星坤科技股份有限公司

生	日期
效	
Δ	
Δ	
Δ	
MARK	DESCRIPTION
文件	工程章
REVISIONS	
DATE	REVISED
APPROVED	
UNSPECIFIED TOLERANCES	

ANGULAR	±5°
X.X	±0.2mm
X.XX	±0.1mm
X.XXX	±0.05mm

DSND	DATE	SCALE: N/A	MODEL TYPE: DC POWER JACK
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	DC-F745
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0