



P.C.B LAYOUT
TOP VIEW



SPECIFICATION

规范

1. Rating: DC 24V 5.0A ;
1. 额定值: DC 24V 5.0A;
2. Contact resistance: $\leq 0.03\Omega$;
2. 接触电阻: $\leq 0.03\Omega$;
3. Insulation resistance: $\geq 100M\Omega$ (DC250V);
3. 绝缘电阻: $\geq 100M\Omega$ (DC250V);
4. Withstand voltage: 500V AC ;
4. 耐压: 500V AC
5. Insertion and extraction force: 3-20N;
5. 插拔力: 3-20N;
6. life test: 5,000 cycles.
6. 寿命试验: 5000次循环

SCHEMATIC	
Model	DC-044B
Center Pin	$\varnothing 2.0$ mm
	$\varnothing 2.5$ mm

	MATERIAL	PLATING
housing	high thermoplastic	silver
terminal2	Phosphor Bronze	silver
terminal3	brass	silver
terminal4	brass	silver
center pin	brass	NI
teminal6	Phosphor Bronze	NI
cover	SUS	

广东星坤科技股份有限公司

生效日期

文件工程章

MARK	DESCRIPTION	REVISIONS	DATE	REVISED	APPROVED

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	DC POWER JACK
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
1.0g	1/1	A0