



Specifications:

规格:

- Voltage rating: 50V AC/DC
- 额定电压: 50V AC/DC
- Current rating: 1A AC/DC
- 额定电流: 1A AC/DC
- Withstanding voltage: 500V AC/minute
- 耐压电压: 500V AC/分钟
- Temperature range: -25°C ~ +85°C
- 温度范围: -25°C ~ +85°C
- Insulation resistance: ≥100MΩ
- 绝缘电阻: ≥100MΩ
- Contact resistance: ≤20mΩ
- 接触电阻: ≤20mΩ
- After environment testing: ≤30mΩ
- 环境试验后: ≤30mΩ

X1102 T X - P V01 X-X

① ②③ ④ ⑤ ⑥ ⑦

- ① Series Number
- ② Category: T-terminal
- ③ Shape: Blank-ordinary
- ④ Material: P-Phosphor bronze
- ⑤ Plating style: V01-Gold Flash
- ⑥ Plating method: Blank-Stamping before plating
- ⑦ Mold No./Mark/Special No.

X1102T-PV01	Phosphor	AWG#28-32	0.80mm(Max)	Stamping Before Plating 30u" Ni/Whole Gold /Gold Flash	X1102H
PART NO	Material	Wire Range	Insulation O.D	Finish	Suitable XKB

广东星坤科技股份有限公司

SECTION: A-A
SCALE: 1:1

SECTION: B-B
SCALE: 1:1

生 日期

文件工程章

REVISIONS

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

www.xkpcb.com www.helloxkb.com www.helloxkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWNN	DATE	VIEW:	PART NO.: 1.00mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	X1102T-PV01
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT SHEET REVISION 1.0g 1/1 A0

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5