



Circuit diagram



PCB Mounting Pattern Dimension



SPECIFICATION

Contact Rating: 50mA, 12V DC
 Contact Resistance: 100mΩ max
 Insulation Resistance: 100mΩ min. 500V DC
 Dielectric Strength: 250V AC/1minute
 Travel: 0.20mm
 Operating Temp: -30°C~+85°C
 Storage Temp: -30°C~+80°C

| | |
|-----------------|-------------------------|
| PAPT NO | TS-1197A-X |
| Operating Force | A:100gf B:160gf C:260gf |
| Height | H:0.55 |
| | |
| | |

| ITEM | PAPT NAMF | TER,NO | QTY | MATERIAL | FINISHING | REMARK |
|------|-----------|--------|-----|---------------|-------------------|--------|
| ⑤ | Terminal | — | 4 | Brass (0.30t) | Plating silvering | — |
| ④ | Contact | — | 1 | F.ag/Sus | Natural | — |
| ③ | Base | — | 1 | Lcp | | — |
| ② | Cover | — | 1 | Brass | Plating Nickel | — |
| ① | Keystake | — | 1 | | | — |

广东星坤科技股份有限公司

生效日期

文件工程章

| REVISIONS | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|-----------|-------------|------|---------|----------|------------------------|
| | | | | | |

| | | | | | | |
|---------------------------------------|--|------|--|-------------|-------------------------|----------|
| DSND | | DATE | | SCALE: N/A | MODEL TYPE: TACT SWITCH | |
| DWN | | DATE | | VIEW: | PART NO.: | |
| CHKD | | DATE | | UNIT: mm/in | DWG NO.: TS-1197A-X | |
| APPD | | DATE | | SIZE: A4 | | |
| KXB INDUSTRIAL PRECISION CO., LIMITED | | | | WEIGHT | SHEET | REVISION |
| | | | | 1.0g | 1/1 | A0 |