



Recommended PCB Layout
(General Tolerance:±0.05)



ITEM	PAPT NAME	QTY	MATERIAL	FINISHING
①	Shell	1	Stainless Steel	
②	Terminal	5	Copper Alloy	
③	Housing	1	HI-TEMP.PLASIC UL 94V-0	BLACK

- Contact Resistance:30m0HM Max.;
- Dielectric Withstanding Voltage:100V AC For 1 Minute;
- Insulation Resistance:1000M OHM Min.;
- Mating And Unmating Force:
Mating Force:35N Max/Unmating Force:8N Min;
- Durability:10000 Cycles;

广东星坤科技股份有限公司

生效日期

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

文件工程章

REVISIONS
www.helloxkb.com www.helloxkb.com www.helloxkb.com

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	MICRO USB
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
			U-E-M5SS-Y-5
			WEIGHT
			1.0g
			SHEET
			1/1
			REVISION
			A0

XKB INDUSTRIAL PRECISION CO.,LIMITED