


- NOTES:**
- ELECTRICAL:**
- 1. VOLTAGE RATING : 125 VAC RMS.
 - 2. CURRENT RATING : 1.5 AMP.
 - 3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
 - 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500 VDC.
 - 5. DIELECTRIC STRENGTH : 1000 VAC RMS 50Hz or 60Hz, 1MIN.
- MECHANICAL:**
- 1. HOUSING & INSERT MATERIAL : PBT UL94V-0.
 - 2. CONTACT MATERIAL : DIAMETER 0.45MM PHOSPHOR BRONZE GOLD PLATING OVER NICKEL.
 - 3. MATING/UNMATING FORCE : 2.28G F MAX.
 - 4. RETENTION STRENGTH : 7.79G F MIN BETWEEN JACK AND PLUG.
 - 5. OPERATING LIFE : 600 CYCLES MIN.
- ENVIRONMENTAL:**
- 1. STORAGE : -10°C ~ +40°C RELATIVE HUMIDITY<70%.
 - 2. OPERATION : 40°C ~ +85°C.



PCB LAYOUT

APPROVED:	DATE:	TITLE:	
CHECKED:	DATE:	RJ45-8P/8C 全塑 弯插 黑色 上带缺口	
DRAWN:	DATE:	PART. NO.	C2902700
SXA	2016-06-21	UNIT	mm
		SCALE	free
		REV.	A HY04
		FILE NO.	R-RJ45R08P-A009

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

深圳市灿科盟实业有限公司
CHANKONGMENG INDUSTRY CO., LTD