



PCB Layout(Pattern side)



Note:
1. Rating: 12V 50mA

NO.1

PART NO	H	4.3	PART NO	H
A	4.3		O	11
B	4.5		P	11.5
C	5		Q	12
D	5.5		R	12.5
E	6		S	13
F	6.5		T	13.5
G	7		U	14
H	7.5		V	14.5
I	8		W	15
J	8.5		X	15.5
K	9		Y	16
L	9.5		Z	16.5
M	10			17
N	10.5			17.5

NO.2

PART NO	Material/Qty
1	vigor 70±30
2	100±50
3	160±50
4	260±50
5	320±80
6	350±80
7	520±130

NO.3

PART NO	Material/Qty
S	SUS/1PC
C	C5210/1PC
D	SUS/2PCS
E	C5210/2PCS

NO.4

PART NO	NOTE
1~9	SERIAL NUMBER

NO.5

PART NO	NOTE
B	Bulk
R	Tape&Reel

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑤	Contact Spring	1	F.Ag/Brass	Plating silver
④	Terminal	4	Brass(0.30t)	Plating silver
③	Base	1	PA	Black
②	Cover	1	SFCC	Plating Nickel
①	KNOB	1	PA	Black

APPROVALS		DATE
DRAWN	G.M.Chen	2014/8/18
CHECKED		
APPROVALS		

DEALON 德之隆
ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	30~0.1±	±0.30	ANGLE	PART NO.	SCALE:	SHEET
	A		NEW				10~0.20	±0.20		UNIT: mm	TC-1101DR-XXN-XXX	1:1	1 OF 1
							5~0.10	±0.10	±2°	DRAWING NO.			PROJ.