




ROHS



Model NO.	PJ-3580B-5A
Schematic	

Rating:0.5A 30V DC
 Contact Resistance:30 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

②	Terminal	5	Phosphor bronze	Ag Plating				
①	Housing	1	PBT	Black				
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK		
APPROVALS			DATE	 ELECTRONICS CO.,LTD				
DRAWN	LIUCAN	2021.6.11	TITLE: PHONE JACKS					
CHECKED			PART NO. PJ-3580B-5A					
APPROVALS			SCALE: 1:1					
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1		
		10~30	±0.20	±2°	DRAWING NO.	PROJ:		
		5~10	±0.15			SHEET 1 OF 1		
		~ 5	±0.10					

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.