





NOTE:
 MATERIAL
 HOUSING: PBT BK UL94V-0.
 CONTACT: COPPER NEEDLES (C2680).
 CONTACT PLATING: GOLD .
 ELECTRICAL
 CURRENT RATING: 3AMP.
 VOLTAGE RATING: 250VAC/DC .
 CONTACT RESISTANCE: 20mΩMAX.
 INSULATION RESISTANCE:1000MΩMIN.
 ENVIRONMENTAL
 TEMPERATURE RANGE: -40°C TO +105°C.
 PACKING: BLISTER BOX (吸塑盒) 98PCS/BOX.

DIMENSION TABLE:

PIN	A (mm)	B (mm)	C (mm)	D (mm)
10	31.90	21.68	10.16	18.32
14	36.98	26.76	15.24	23.40
16	39.52	29.30	17.78	26.23
20	44.60	34.38	22.85	31.32
26	52.22	42.00	30.46	38.94
30	57.30	47.08	35.56	44.02
34	62.38	52.16	40.64	49.10
40	70.00	59.78	48.26	56.72
50	82.70	72.48	60.96	69.42
60	95.40	85.18	73.66	82.12
64	100.48	90.26	78.74	87.20



PCB LAYOUT

ROHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	针座	料号	CS-1200WS-34 (L16mm 短耳)			材料	单位	mm	SHEET 1 OF 1			
	版本	A/0	设计	李文畅	X.X	±0.20	颜色	比例	1:1	▲1	修改内容	修改日期
	制定部门	工程部	绘制	李文畅	X.XX	±0.10	画法	数量	⊕	▲1		
	工程图号	CST-1200WS	审核	姚培柱	X.XXX	±0.05	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.			▲2		
	制定日期	2018/04/04	核准	周中湖	X.XXXX	±0.01				▲3		