



PCB LAYOUT

NOTE:

MATERIAL

HOUSING: PBT BK UL94V-0  
 CONTACT: C2700.  
 CONTACT PLATING: GOLD OVER Nickle

ELECTRICAL

CURRENT RATING: 3AMP.  
 VOLTAGE RATING: 250VAC/DC.  
 DIELECTRIC WITHSTANDING VOLTAGE: 600VAC MIN.  
 CONTACT RESISTANCE: 20mΩ MAX.  
 INSULATION RESISTANCE: 1000MΩ MIN.

ENVIRONMENTAL

TEMPERATURE RANGE: -40° C TO +105° C.

DIMENSION TABLE: 注: 2\*40 P A尺寸不用減0.25mm

Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
2 * 2	5.08	2.54	2 * 15	38.10	35.56	2 * 28	71.12	68.58
2 * 3	7.62	5.08	2 * 16	40.64	38.10	2 * 29	73.66	71.12
2 * 4	10.16	7.62	2 * 17	43.18	40.64	2 * 30	76.20	73.66
2 * 5	12.70	10.16	2 * 18	45.72	43.18	2 * 31	78.74	76.20
2 * 6	15.24	12.70	2 * 19	48.26	45.72	2 * 32	81.28	78.74
2 * 7	17.78	15.24	2 * 20	50.80	48.26	2 * 33	83.82	81.28
2 * 8	20.32	17.78	2 * 21	53.34	50.80	2 * 34	86.36	83.82
2 * 9	22.86	20.32	2 * 22	55.88	53.34	2 * 35	88.90	86.36
2 * 10	25.40	22.86	2 * 23	58.42	55.88	2 * 36	91.44	88.90
2 * 11	27.94	25.40	2 * 24	60.96	58.42	2 * 37	93.98	91.44
2 * 12	30.48	27.94	2 * 25	63.50	60.96	2 * 38	96.52	93.98
2 * 13	33.02	30.48	2 * 26	66.04	63.50	2 * 39	99.06	96.52
2 * 14	35.56	33.02	2 * 27	68.58	66.04	2 * 40	101.60	99.06

RoHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有, 未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	针座	料号	CS-1107-2*10 (L10.8/15.8)		
版本	B/0	设计	李文畅	X.X	±0.20
制定部门	工程部	绘制	李文畅	X.XX	±0.10
工程图号	CS-1107	审核	姚培柱	X.XXX	±0.05
制定日期	2020-11-20	核准	周中湖	X.XXXX	±0.01

材料	单位	mm	SHEET 1 OF 1	
颜色	比例	1:1	▲1	修改内容
画法	数量		▲1	修改日期
CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO., LTD.			▲2	
			▲3	