



环保物料

TEL: 0769-82001899



SPECIFICATIONS

- 1.Voltage rating: 50V AC, DC
- 2.Current rating: 2A, AC, DC
- 3.Withstanding Voltage: 500V AC/minute
- 4.Insulation resistance:100M Ω min
- 5.Temperature range: -25 ° C-+85 ° C
- 6.Contact resistance: 20m Ω max

WAFER

Housing Material: PA4T UL 94V0

Pin Material: Phosphor Bronze or Brass

Contact Area Plating: Plated Tin or Plated Gold





Mates with :P1201 series Housing

Poles:02-15P

Part No.: M1201RS-xx-BK

Pin位数

CKT	Dim A	Dim B	DimC
2	1.2	2.6	4.2
3	2.4	3.8	5.4
4	3.6	5.0	6.6
5	4.8	6.2	7.8
6	6.0	7.4	9.0
7	7.2	8.6	10.2
8	8.4	9.8	11.4
9	9.6	11.0	12.6
10	10.8	12.2	13.8
11	12.0	13.4	15.0
12	13.2	14.6	16.2
13	14.4	15.8	17.4
14	15.6	17.0	18.6
15	16.8	18.2	19.8



5PIN 以上加逃料

				TOLERANCE UNLESS OTHERWISE		DRAWN		CK tan		SHEET		1/1	
				X. ± 0.30 X° $\pm 5^\circ$		CHKD				DATE		2020. 04. 12	
				.X ± 0.20 .X° $\pm 2^\circ$		APPD		PRODUCT NAME		UNITS		mm	
				.XX ± 0.08 .XX° $\pm 1^\circ$		VIEW		PART. NO.		SCALE		1:1	
AO				.XXX ± 0.03 .XXX° $\pm 0.5^\circ$		VIEW		M1201RS-xx-BK		DWG. NO.		009	
VER				MODIFICATION		DRAW		DATE					