


# Kinghelm®

REVISIONS			
REV NUMBER	DESCRIPTION	DWN	CHK
A	DESIGN		



**NOTES:**

1. ELECTRICAL:
  - 1.1. VOLTAGE RATING:DCV 300V 10MS
  - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
  - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - 1.5. IT SHOULD BE NO ANY OPENS/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
  - 2.1. SEE TABLE
3. ALL COMPONENTS ARE ROHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	高仿I-PEX, 1.13端子, 镀金	1
②	接头	SMA母头母针, 带4个脚, 11牙, 镀金	1
①	同轴线	RF1.13黑线, OD:1.13mm	AS

深圳市金航标电子有限公司 WWW.BDS666.COM

KH-IPEXA-SMAKWE-B060H 0755-83044319

ALL DIMENSION ARE IN MM		DRAWN		DATE	
CHKD.	James	James	2021-10-30		
APPD.	Frank	Frank	2021-10-30		
COMPUTER GENERATED IN SOLIDWORKS		APPD.	Scott	2021-10-30	

DO NOT SCALE THIS DRAWING		GENERAL TOLERANCE FOR ANGLES	
± 1° ±	0.5	0.25	0.150

PROJECTION	SCALE	TYPE	SHEET	REV
	B	K:XXX	1	A

CUSTOMER P/N:

I-PEX 1.13 TO SMA /F L=60mm

SIZE/Number

SCALE: Free

TYPE

SHEET 1

OF