

5



4

3


2

1


D




C




Panel cut out



B



A

Mod.	Dat.	Name	Detail.	Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, female, straight, 9 poles, for crimp contacts, tin plated shell	Maßstab/ Scale 1,5:1
34784	13/02/08	PK						
33106	22/09/05	JMDR	Insp.	09/04/02	CV			
31571	12/11/03	SH	Stand.					
31526	31/07/03	TCP	HARTING EURL F-95972 Paris				TB 09 67 009 4701	Blatt/ Page 1 / 2
29768	09/04/02	CV						