







SPECIFICATIONS:

Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +105°C
 Contact Resistance: 20mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1000V AC/minute
 Pin Material: Brass/Tin over Nickel
 SMT Material: Brass/Tin over Nickel
 Material: LCP, UL94V-0(Beige)

Ordering Information & Dimensions

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2P	2.50	6.00	10.00	10P	22.50	26.00	30.00
3P	5.00	8.50	12.50	11P	25.00	28.50	32.50
4P	7.50	11.00	15.00	12P	27.50	31.00	35.00
5P	10.00	13.50	17.50	13P	30.00	33.50	37.50
6P	12.50	16.00	20.00	14P	32.50	36.00	40.00
7P	15.00	18.50	22.50	15P	35.00	38.50	42.50
8P	17.50	21.00	25.00	16P	37.50	41.00	45.00
9P	20.00	23.50	27.50				



CJTconn

CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	4:1	1 of 1

Draw BY:	Approved :
LIZQ	GONGYB

General Tolerance

ANGLE±

Title :
 2.50mm PITCH
 180° WAFER-SMT TYPE

DRAW NO : A2501WV-S-XP REV A0

REV	DESCRIPTION	DATE
A0	NEW RELEASE	2013.04.27